

DV-7000 Heli-Flow[®] Pump

Servo-controlled auger pump

Features and Benefits

- Ideal for small precise dots of solder paste, silver epoxy, and surface mount adhesive
- Footed cartridge with a fixed mechanical stand-off nozzle for extremely consistent dots and increased throughput
- Luer-cartridge option allows use with a wide range of standard needles
- Tool-free disassembly of wetted parts for quick and easy cleaning
- Fast cartridge changeover
- Cartridges are interchangeable with DV-8000 pumps



The DV-7000 Heli-Flow Pump is available in a luer- or footed-needle design with interchangeable cartridges, allowing each pump to work with several different fluid types. The DV-7000 has a hardened auger for use with filled epoxy materials and features a high flow rate.

Footed needle cartridges feature an accurate and consistent gap between the needle tip and the foot. The foot contacts the board, and the gap ensures that the pump dispenses fluid at a programmable distance from the board surface and compensates for variations in the board's surface, providing fast small-dot dispensing. Typical applications include solder paste, silver epoxy, and dispensing small-dot surface mount adhesives.

Luer-lock needle cartridges use the needle with a height sensor to set the gap between the board surface and needle tip, and is ideal for applications when the needle can not touch the board. Applications include dam writing, area fills, glob top, and lid seal.

The quick-release cartridge design of the DV-7000 makes cleaning easy. Simply press the quick release lever to remove the needle and cartridge. No tools are required. To use a different fluid type, simply change the cartridge, needle, and disposable fluid line.

Nordson ASYMTEK's other auger pump – the DV-8000 with its fixed-head design – is ideal for high flow rate encapsulation and lid seal applications. The DV-7000 pump is interchangeable with DV-8000 cartridges, although only the DV-7000 can use footed cartridges. Both pumps cover a wide range of dispensing applications to provide flexible process solutions.

DV-7000 Heli-Flow[®] Pump Specifications and Configurations

Dimensions

Length: 190-192 mm (7.48-7.56 in.)
 Width: 33 mm (1.3 in.)
 Depth: 72.6 mm (2.86 in.)

Air Pressure Required


34-552 kPa (0.7-5.5 Bar, 5-80 psi)
 Higher fluid viscosities require higher pressures

Motor

Closed-loop control with encoder feedback on the dispensing platform

Pump Configurations

Model	Description	Application
DV-7222-SF1	Footed needle cartridge	Surface mount adhesive, solder paste, silver epoxy
DV-7222-SL1	Luer-lock needle cartridge	Surface mount adhesive, solder paste, silver epoxy
DV-7223-CP8-LP	Precision needle cartridge	Silver epoxy, Types 3 and 4 solder pastes
DV-7223-CP0-LP	Precision needle cartridge	Types 5 and 6 solder pastes
DV-7321-CL8	Luer-lock needle cartridge	Dam writing
DV-7322-CL8	Luer-lock needle cartridge	Glob top, encapsulation
DV-7331-CL8	Luer-lock needle cartridge	Lid seal



Nordson ASYMTEK
+1.760.431.1919 Phone
info@nordsonasymtek.com **Email**
2747 Loker Avenue West
Carlsbad, CA, USA 92010-6603
www.nordsonasymtek.com

Published 2016-07-18

Page 2 of 2

For more information, speak with your local representative or contact your regional office.

Nordsonasymtek.com

North America

Headquarters
 Carlsbad, CA, USA
 +1.760.431.1919
info@nordsonasymtek.com

China

Email: china-info@nordsonasymtek.com

Shanghai
 +86.21.3866.9166

Beijing
 +86.10. 8453.6388

Guangzhou
 +86.20.8554.9996

Europe

Maastricht, Netherlands
 +31. 43.352.4466
cs.europe@asymtek.com

Japan

Tokyo
 +81.3.5762.2801
Info-jp@nordsonasymtek.com

Korea

Seoul
 +82.31.765.8337
info@nordsonasymtek.com

India

Chennai
 +91. 44.4353.9024
info@nordsonasymtek.com

S.E. Asia/Australia

Singapore
 +65.6796.9514
info@nordsonasymtek.com

Taiwan

+886.229.02.1860
info@nordsonasymtek.com

