

Genuine Nordson Replacement Parts



Saturn® family of products

Color-coded rings identify key characteristics to simplify replacement and troubleshooting.

Saturn nozzles* provide superior pattern placement, bead consistency and cutoff for less downtime, better bonding and adhesive savings. Rings identify orifice and engagement or orifice and angle. Nozzles are available in single- and dual-orifice, right-angle and specialty designs.



Saturn solenoid valves** optimize hot melt dispensing gun performance with high air-flow capacity for better cutoff and high-temperature seals for longer life. Rings identify voltage and air flow (Cv value). Designed specifically for hot melt adhesive dispensing, valves are available in 3-way and 4-way air-open/spring close and air-open/air-close designs.

Saturn inline filters* trap contaminants and char to reduce nozzle clogging and improve gun performance. Rings identify filter mesh size. Filter assemblies are available in straight, 45-degree and 90-degree configurations. Value packs of 3 or 5 filter elements help you save.

* Patented

** Patent pending

Nordson replacement gun modules

Nordson **ClassicBlue™**, **SolidBlue™**, **SureBead®** and **MiniBlue™** replacement gun modules deliver long service life and easier maintenance. Myritex™ seals improve module reliability and performance. Shared components increase serviceability and decrease inventory needs.




ClassicBlue module



SolidBlue module



SureBead module



MiniBlue module

Hoses

Nordson **RTD** and **TC hoses** operate with proven durability and performance, reducing costs and downtime. Parallel ground paths and make-first, break-last electrical pins provide safer operation. Flexible, aramid insulation improves chemical and moisture resistance and does not melt or support combustion. A Teflon® core, superior heating element and sensing accuracy provide consistent flow rates.



Select Series™ Guns and Hoses

Now you can significantly improve the performance of your ITW Dynatec, Robatec, Inc. and HMT (Hot Melt Technologies, Inc) automatic or manual hot melt systems with Nordson Select Series gun and hoses. You will benefit from more consistent flow rates, improved adhesive cutoff and enhanced operator safety.



Spend a Little, Save a Lot

Nordson insulating Saturn filter jackets and pneumatic gun jackets reduce energy consumption, protect operators and improve adhesive flow.



Melter flushing kits contain everything you need (including step-by-step instructions) for do-it-yourself melter cleaning and flushing. Regular cleaning removes excess dirt and charred material that can cause poor performance. You should also flush your melter each time you change to a new adhesive formulation.

Nordson has a comprehensive inventory of over 50,000 parts to support all Nordson systems and keep your equipment running at peak performance.

To view a complete listing of Nordson parts see our Replacement Parts Catalog or visit www.enordson.com. To order call (888) NORDSON (667-3766) or visit www.enordson.com. Printed copies of the Nordson Replacement Parts Catalog are also available upon request.

*Teflon is a registered trademark of E.I. DuPont de Nemours & Co.
Rings are a trademark of Nordson Corporation*

For more information, talk with your Nordson representative or contact your Nordson regional office.

United States

Duluth, Georgia
Telephone: (800) 683-2314
Toll-free Facsimile:
(866) 667-3329

Canada

Markham, Ontario
Telephone: (800) 463-3200
Facsimile: (905) 475-8821

Europe

Lüneburg, Germany
Telephone: (49) 4131-894-0
Facsimile: (49) 4131-894-149

Japan

Tokyo, Japan
Telephone: (81) 3-5762-2700
Facsimile: (81) 3-5762-2701

Asia/Australia/ Latin America

Amherst, Ohio
Telephone: (440) 985-4797
Facsimile: (440) 985-1096

www.nordson.com



When you expect more.®

Nordson Corporation • 11475 Lakefield Drive • Duluth, Georgia 30097-1511