

Xaloy[®] Front End Components

- Consistency
- Repeatability
- Improved Wear Life
- Cost Effectiveness
- Peak Performance
- Up Front Where It Means The Most!


Nordson can design and manufacture a complete line of Xaloy front end components for injection units from a variety of abrasion and corrosion resistant steels including: Hastelloy, Inconel, M390, H13, D2, S7, CPM and 17-4PH stainless steel.

Components include:

- End Caps
- Nozzle Tips
- Nozzle Bodies
- Non-Return Valves

Nordson's comprehensive line of Xaloy front end components are made to OEM original specifications with improved wear and corrosion resistance.

Select from a broad range of materials of construction and top that with fast delivery, maximizing your up time.



Auto-Shut[™] Valves

1. Free flowing, positive shutoff, self-cleaning
2. Most consistent shot-to-shot repeatability in the industry
3. Shut-off mechanism operates independent of screw travel
4. Poppet style design eliminates problems associated with retainer wear
5. Generous poppet stroke for reduced pressure drop
6. Spring-actuated, instantaneous closing, independent of resin viscosity

Advantages:

- Best shot repeatability in the industry
- Mechanical shutoff
- Reduced splay and silver streaking
- Eliminates retainer wear
- Free flowing

Benefits:

- Consistent performance
- Superior shot control
- Less scrap produced
- Extended service life
- Reduced shear and black specks

Applications:

1. PC and ABS alloys
2. Acrylic
3. Polyolefins with 10 MI or less
4. Not for use with nylons and glass-filled materials

FTR[™] Valves

1. Three-piece non-return valve
2. Free flow design with zero restriction
3. Greater contact area for reduced wear
4. Self-cleaning design
5. Economical

Benefits:

- Improved wear
- Eliminates burning and black specks
- Longer service life
- Greater processing flexibility
- Low part weight deviation
- The best RPVC 3-piece valve available

Applications:

1. RPVC

Advantages:

- Free flow design
- Excellent shot repeatability
- Self-cleaning
- Greater contact area
- Low shear design

Xaloy® Front End Components



Sliding Ring Valves

1. Industry standard design
2. Flow path design can be tailored to wide range of resins
3. Materials of construction range from standard H13 and D2 tool steels to high performance CPM grades
4. Available in three- and four-piece configurations
5. Economical

Applications:

1. General purpose
2. Special four-piece “shear eliminating” designs for fluoropolymer materials

Advantages:

- Wide range of resins
- Variety of construction materials
- Durability
- Versatile three and four-piece configurations
- Low cost

Benefits:

- General purpose design
- User-selectable levels of wear performance
- Good for custom molding applications
- Replaceable components
- Low investment



Locking Ring Valves

1. Zero relative velocity ring/retainer interface
2. Streamlined design for smooth lock-up
3. Flow paths can be tailored to a wide range of resins
4. Reduced valve wear with abrasive resin compounds

Applications:


1. General purpose with abrasive fillers

Advantages:

- Zero velocity between ring and retainer
- Variety of construction materials
- Good shot repeatability
- Flow paths can be tailored to accommodate a wide range of resins

Benefits:

- Resists ring/retainer wear
- Improved wear life in abrasive applications
- General purpose three-piece design
- Consistent part weights
- Good in custom molding applications



Poly-Check® Valves

1. Ball check with optimized flow path design
2. Self-cleaning configuration
3. Simple front discharge, no inserts or thread-on components
4. Superior shot repeatability
5. Simple one-piece design adds to durability and promotes longer wear life with standard materials of construction

Applications:

1. All polyolefin-based materials with greater than 8 MI
2. Polystyrene
3. LSR

Advantages:

- Dependable design
- Self-cleaning
- Superior shot repeatability
- Ball seat is easily resurfaced
- Few moving parts
- Low cost
- Reduced wear in larger diameters

Benefits:

- Easy to maintain
- Low part weight deviation
- Good wear performance
- Can be rebuilt by re-seating and installing new ball
- Low investment



Eliminator® Nozzle Tips

Advantages:

- Eliminates stringing, drooling, cold slugs
- Hardened steel, easy installation, universal design

Benefits:

- Eliminates costly mold repair caused by strings pulling across mold face
- Works on highly crystalline, semi-crystalline and shear-sensitive materials

Nordson Xaloy Incorporated
1399 Countyline Road
New Castle, PA 16101 USA
+1.724.656.5600 **Phone**

Germany
+49.7132.999.35.0 **Phone**

Thailand
+66.38.717.084 **Phone**

China
+86.21.5785.091.8 **Phone**

www.nordsonpolymerprocessing.com | info@nordsonpolymerprocessing.com

© 2015 Nordson Xaloy
Printed in USA
8/2016

